

IDRA II

TECHNICAL

GUIDE

CONTENTS

DIMENSIONS AND WEIGHT	P. 3
-----------------------	------

WHAT'S INCLUDED	P. 3
-----------------	------

PC SPECS REQUIREMENTS	P. 4
-----------------------	------

POSITIONING SPECIFICATIONS	P. 5
----------------------------	------

DIMENSIONS AND WEIGHT



WEIGHT: 14.4 LBS

- A** WIDTH: 13 5/16"
- B** HEIGHT: 7 1/4"
- C** DEPTH: 9 5/8"

Ensure that you have sufficient space to comfortably swing your club in your chosen area.

WHAT'S INCLUDED

- IDRA II camera
- Calibration board
- IDRA II ceiling mount
- Wireless remote control outlet (Only included in North America)
- 1/2" drywall plastic toggle anchors (4)
- 1" head Phillips/square drive screws (4)
- 3" head Phillips/square drive screws (4)
- 2 years warranty

PC SPECS REQUIREMENTS

WITH GSPRO

Processor

Minimum

Intel i7 10th gen + 16 logical processors

Recommended

Intel i7 10th gen + 24 logical processors

Storage

Minimum

512 GB

Recommended

1 TB

USB Ports

2 USB 3.0 ports are required

GPU

Minimum

Nvidia GeForce RTX 20 series

Recommended

Nvidia GeForce RTX 40 series

RAM memory

Minimum

16 GB

Recommended

32 GB

Internet

High speed internet is required

WITH E6 CONNECT

Processor

Minimum & recommended

Intel i7 10th gen + 16 logical processors

Storage

Minimum & recommended

512 GB

USB Ports

2 USB 3.0 ports are required

GPU

Minimum

Nvidia GeForce RTX 20 series

Recommended

Nvidia GeForce RTX 30 series

RAM memory

Minimum & recommended

16 GB

Internet


High speed internet is required



WARNING

- AMD processors are NOT supported.
- DO NOT use USB cable extension between your PC and your IDRA II camera.

POSITIONING SPECIFICATIONS



Camera Height (inches)	99	100	101	102	103	104	105	106	107	108	109
Ball to cam position (inches)	47 3/4	48 1/4	48 3/4	49 1/4	49 3/4	50 1/8	50 5/8	51 1/8	51 5/8	52 1/8	52 5/8

Camera Height (inches)	110	111	112	113	114	115	116	117	118	119	120
Ball to cam position (inches)	53 1/8	53 1/2	54	54 1/2	55	55 1/2	56	56 1/2	56 7/8	57 3/8	57 7/8

The PC must be positioned within a maximum of 25 feet from IDRA II.